

RESULT OF SALT SPRAY TESTING



AKIYAMA SEIKO CO.,LTD.

18-8

18 Cr

13 Cr





AFTER PLATING

ASK-3000T

DHS 1

ASK-3400L

ASK-2300 (CM) THICKNESS : 5 μ m





ASK-3000S

ASK-3200

ASK-3400T

ASK-2300 (CM) THICKNESS : 10 μ m






ASK-3000U

ASK-3300F

ASK-3700

ASK-2300 (G) THICKNESS : 5 μ m




ASK-3000FL

ASK-3300T

ASK-3500A

ASK-2300 (G) THICKNESS : 10 μ m



SUS 304

JIS Z 2371 (35°C 5%NaCl 96 hrs.)

Sample φ10.00×150
(2μmRy)

OTHERS ASK-8000

